

HORUS RANGE

THERMOPLASTIC FLOODLIGHTS












GEWISS

SELECTION GUIDE



HORUS RANGE

					HORUS 1		HORUS 2			
										
TECHNOLOGY	POWER SUPPLY UNIT	POWER LP	ILCOS NAME	LAMP TYPE	DIFF. SYMM.	DIFF. ASYMM.	DIFF. SYMM.	DIFF. ASYMM.	RESTR. CIRC.	
Discharge lamps	Magnetic	70W	SD		GW 85 302	GW 85 301	GW 85 001	GW 85 031	GW 85 051	
		70W	MD		GW 85 302	GW 85 301	GW 85 001	GW 85 031	GW 85 051	
		70W	ST					GW 85 032		
		70W	ST *				GW 85 005			
		150W	SD				GW 85 002	GW 85 033	GW 85 052	
		150W	MD				GW 85 002	GW 85 033	GW 85 052	
		80W	QE				GW 85 003			
		100W	ME				GW 85 004			
	Unwired	Max 70W	-	-		GW 85 393	GW 85 391		GW 85 094	
		Max 100W	-	-				GW 85 092		
Max 150W		-	-				GW 85 091	GW 85 093	GW 85 095	
Fluorescent	Magnetic	2x18W	F5Q		GW 85 306					
	Unwired	2x18W	-	-	GW 85 392					
	Magnetic	4x18W	F5D				GW 85 006			
	Electronic	42W	F5Q		GW 85 366					
		32W Em.	F5Q		GW 85 367					
	Unwired	42W	-	-	GW 85 396					
	Electronic	2X42W	F5Q				GW 85 066			
		2X42W Em.	F5Q				GW 85 307			
Unwired	2X32W	-	-			GW 85 097				


* Lamp without built-in ignitor.

					HORUS 3					
										
TECHNOLOGY	POWER SUPPLY UNIT	POWER LP	ILCOS NAME	LAMP TYPE	DIFF. SYMM.	DIFF. ASYMM.	RESTR. SYMM.	RESTR. ASYMM.	ROAD	
Discharge lamps	Magnetic	150W	ST						GW 85 241	
		250W	ST		GW 85 101	GW 85 131	GW 85 201	GW 85 221	GW 85 242	
		250W	MT		GW 85 101	GW 85 131	GW 85 201	GW 85 221	GW 85 242	
		250W	MT (1KV)		GW 85 102	GW 85 132	GW 85 202	GW 85 222		
		250W	QE		GW 85 103					
		400W	ST		GW 85 104	GW 85 133	GW 85 203	GW 85 223		
		400W	MT		GW 85 104	GW 85 133	GW 85 203	GW 85 223		
		400W	MT (1KV)		GW 85 105	GW 85 134	GW 85 204	GW 85 224		
		Max 250W	Unwired							GW 85 293
		Max 400W	Unwired			GW 85 191	GW 85 192	GW 85 291	GW 85 292	
Fluorescent	Electronic	120W	F5Q		GW 85 109	GW 85 149				
		120W	F5Q		GW 85 110	GW 85 150				


HORUS 1




installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4x3	354	247	0.7
5m	6x5	182	137	0.75
10m	10x8	38	27	0.71




installation height	L1xL2	d	E max	E med.	UNIFORMITY
3m	3.5x2.5	1.5m	292	176	0.6
5m	5x4.5	3m	113	60	0.53
10m	9.5x7.5	5m	29	16	0.54



installation height	L1xL2	E max	E med.	UNIFORMITY
3m	5x4	14	10	0.7
5m	8.5x5.5	5	3.5	0.76







installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4x3	80	48	0.6
5m	6x5	29	18	0.63



installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4x4	12	8	0.7
5m	6x5	5	3.1	0.68






HORUS 2



installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4.5x2	792	405	0.51
5m	7x2	322	215	0.67
10m	13x3.5	85	62	0.73

installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4x2	321	241	0.63
5m	6.5x3	116	91	0.69
10m	13x5.5	29	26	0.74

installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4x2	321	223	0.69
5m	7x3.5	116	86	0.75
10m	14x6.5	29	21	0.73



installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4x5	61	40	0.67
5m	7x8	22	14	0.66
10m	12x14.5	6	4	0.7

installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4.5x4	80	53	0.66
5m	7x6	29	19	0.67
10m	15x13	7	4	0.6

installation height	L1xL2	E max	E med.	UNIFORMITY
3m	4x2	12	8	0.7
5m	6x5	5	3.1	0.68
10m				

HORUS RANGE


HORUS 2

150W MD CIRCULAR OPTICS						150W MD ASYMMETRICAL OPTICS						70W ST ASYMMETRICAL OPTICS					
installation height	L1xL2	E max	E med.	UNIFORMITY		installation height	L1xL2	d	E max	E med.	UNIFORMITY	installation height	L1xL2	d	E max	E med.	UNIFORMITY
5m	1.5x1.5	1668	1223	0.73		3m	4.5x2.5	1.5m	419	313	0.75	3m	4.5x3	2m	192	120	0.62
10m	3x2	555	350	0.63		5m	8.5x4	2.5m	150	107	0.71	5m	8x5	3m	69	45	0.65
15 m	4x2.5	278	190	0.68		10m	16.5x7.5	5m	38	27	0.72	10m	15x19.5	6.5m	17	11	0.66


HORUS 3

400W MT DIFFUSED SYMMETRICAL OPTICS						400W MT DIFFUSED ASYMMETRICAL OPTICS						400W MT RESTRICTED BEAM SYMMETRICAL OPTICS					
installation height	L1xL2	E max	E med.	UNIFORMITY		installation height	L1xL2	d	E max	E med.	UNIFORMITY	installation height	L1xL2	E max	E med.	UNIFORMITY	
10m	13x4	239	157	0.66		10m	14.5x5	5m	141	94	0.63	10m	13.5x2.5	342	205	0.6	
13m	17x5	143	94	0.66		13m	18.5x6	7m	83	53	0.69	13m	17.5x3	207	138	0.67	
16m	21.5x6	95	63	0.66		16m	23x7.5	9m	55	38	0.74	16m	21.5x4	84	88	0.64	


HORUS 3





installation height	L1xL2	d	E max	E med.	UNIFORMITY
10m	13x2.5	5.5m	216	136	0.63
13m	17.5x3.5	7m	129	83	0.64
16m	21x4	9m	86	54	0.63



installation height	L1xL2	E max	E med.	UNIFORMITY
8 m	20x8	84	50	0.6
10m	24x10	54	32	0.59
12m	29x12	37	22	0.58



installation height	L1xL2	E max	E med.	UNIFORMITY
5m	7x4.5	120	86	0.72
7m	9.5x6	63	43	0.68
10m	14x8.5	31	21	0.68



installation height	L1xL2	d	E max	E med.	UNIFORMITY
5m	7x5	2.5m	104	64	0.62
7m	9x6	3.5m	56	36	0.64
10m	13x10	5.5m	27	17	0.64